CHD-4U



SYSTIMAX® CHD 4U sliding tray fiber panel, accepts (48) CHD ULL modules, splice cassettes or MPO panels, providing up to 288 duplex LC ports or up to 288 MPO ports, black, High Speed Migration

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series CHD

General Specifications

Application Accepts 48 CHD Universal Modules, or CHD MPO/LC adapter packs

Rack Units 4

Shelf Movement Sliding

Dimensions

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 538.48 mm | 21.2 in

Packaging and Weights

Weight, net 15.604 kg | 34.4 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



