

# FGS-HNTS-1/2

---



FiberGuide® Top Support C-Bracket Kit, 1/2in for 2x6, 4x4, 4x6in Systems

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket
<b>Bracket Type</b>	C-bracket
<b>Bracket Installation Type</b>	No Brackets
<b>Attachment Type</b>	Threaded rod

## Dimensions

<b>Height</b>	304.8 mm   12 in
<b>Width</b>	38.1 mm   1.5 in
<b>Length</b>	203.2 mm   8 in
<b>Thread Size</b>	1/2 in
<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   51 mm x 152 mm (2 in x 6 in)

## Ordering Tree

# FGS-HNTS-1/2

FGS - HNTS - <sup>9</sup>F - <sup>10</sup>5/8 - <sup>11</sup>A

## For Section Size

9	empty	4 x 4 in, 4 x 6 in
	F	4 x 12 in

## For Threaded Rod Size

10	1/2	1/2 in
	1/2-LP	1/2 in, low profile
	12MM	12 mm
	12MM-LP	12 mm, low profile
	14MM	14 mm
	14MM-LP	14 mm, low profile
	16MM	16 mm
	16MM-LP	16 mm, low profile
	5/8	5/8 in
	5/8-LP	5/8 in, low profile

11	A	Adjustable
----	---	------------

## Material Specifications

**Material Type** Carbon steel

## Packaging and Weights

**Included** Hardware | Locking Washers | Nuts | Quick Knobs | Screws | Washers

**Packaging quantity** 1

**Weight, net** 0.962 kg | 2.121 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS  
REACH-SVHC  
ROHS  
UK-ROHS

### Classification

Below maximum concentration value  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](https://www.commscope.com/ProductCompliance)  
Compliant  
Compliant

