FGS-ISLAND-H/F



FiberGuide® Island T, 4x24in, 4x12in Exit Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Tee

Product Brand FiberGuide®

Product Series FGS

General Specifications

Color Yellow

OrientationHorizontalSection TypeTee section

Dimensions

 Height
 120 mm | 4.724 in

 Width
 610 mm | 24.016 in

 Length
 795 mm | 31.299 in

System Dimensions 102 mm x 305 mm (4 in x 12 in) | 102 mm x 610 mm (4 in x 24 in)

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 2.9 kg | 6.393 lb

Page 1 of 2

FGS-ISLAND-H/F

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

