

LSX-7L/OZC031



LSX Fiber Termination Chassis 4 RU, 96 - SC/APC, Singlemode IFC Stranded, 31 Meters, Far end connection Stub

Product Classification

| | |
|------------------------------|-------------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch chassis, with IFC cable |
| Product Series | LSX |

General Specifications

| | |
|------------------------------|-------------------------------|
| Functionality | Patching |
| Application | Used in LSX-style frames only |
| Cable Exit Location | Upward |
| Cable Stub Type | IFC, stranded |
| Color | Putty white |
| Growth Configuration | Fully loaded |
| Interface, front | SC/APC |
| Interface, rear | Stub tail |
| Rack Type | EIA 19 in EIA 23 in |
| Rack Units | 4 |
| Shelf Movement | Fixed |
| Total Ports, quantity | 96 |

Dimensions

| | |
|---------------------|-------------------|
| Height | 177.8 mm 7 in |
| Width | 482.6 mm 19 in |
| Depth | 304.8 mm 12 in |
| Cable Length | 31 m 101.706 ft |

LSX-7L/OZC031

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

