


FBR-COIL-S



HELIAX® Excess Discrete Fiber Coiling Reel, accommodates 16ft (5m) of excess 7mm fiber, weights 5lbs fully populated, stackable, PIM free

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor storage coil
Product Brand	HELIAX®

General Specifications

Color	Black
Mounting	Angle iron Pipe, 44–88.9 mm (1.75–3.5 in) OD

Dimensions

Height	203.2 mm 8 in
Width	139.7 mm 5.5 in
Depth	50.8 mm 2 in

Material Specifications

Material Type	Plastic
----------------------	---------

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Indoor Outdoor

Packaging and Weights

Included	Mounting hardware
Weight, net	0.454 kg 1 lb

FBR-COIL-S

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

