760244561 | FACT-MMDRME-B



FACT® MPO Module, right sided, LC/APC at front side, 2x12 fiber MPO at rear side, singlemode, wiring method B Enhanced

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber module

Product Brand FACT®
Product Series FACT

General Specifications

Functionality Breakout

Application For Use with FACT NG4 Universal Chassis

Body Style Right orientation

 Color, boot
 Black

 Color, housing
 Black

 Color, rear
 Green

 Interface, front
 LC/APC

 Interface Feature, front
 Simplex

 Interface Color, front
 Green

 Interface, rear
 MPO

Interface Feature, rear Female | Key up/up | Unpinned

Interface Color, rear Green

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 24

Total Ports, quantity, front 24

Total Ports, quantity, rear 2



760244561 | FACT-MMDRME-B

Dimensions

 Height
 13.21 mm | 0.52 in

 Width
 159.77 mm | 6.29 in

 Depth
 122.68 mm | 4.83 in

Optical Specifications

Fiber ModeSinglemodeInsertion Loss, maximum0.75 dBInsertion Loss, typical0.6 dBReturn Loss, minimum62 dB

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to $+40 \,^{\circ}\text{C}$ ($+23 \,^{\circ}\text{F}$ to $+104 \,^{\circ}\text{F}$)

Storage Temperature $-5 \,^{\circ}\text{C}$ to $+50 \,^{\circ}\text{C}$ ($+23 \,^{\circ}\text{F}$ to $+122 \,^{\circ}\text{F}$)

Relative Humidity Up to 85%, non-condensing

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

