

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © 2016 Commscope, INC. Confidential NOTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
D		REVISED PER ECN# 8000019965	18FEB17	HSM/JCA

PART NUMBER	FIBER TYPE 	MAX ATTENUATION (dB/km)				MINIMUM OVERFILLED LAUNCH BANDWIDTH (MHz*km)		MINIMUM EFFECTIVE MODAL BANDWIDTH (MHz*km)	MINIMUM 10 GIGABIT ETHERNET LINK DISTANCE (meters)	JACKET COLOR 	FIBER SPECIFICATION
		850nm	1300nm	1310nm	1550nm	850nm	1300nm	850nm	850nm		
4-2193059-9	OM4	3.0	1.0	N/A	N/A	3500	500	4700	550	AQUA	TIA-492AAAD CS 115-32023 CLASS 2
6-2193059-1	62.5/125 OM1	3.5	1.2	N/A	N/A	200	500	N/A	33	BLACK	TIA-492AAAA
6-2193059-2	50/125 OM2	3.5	1.5	N/A	N/A	500	500	N/A	82	BLACK	TIA-492AAAB CS 115-32023 CLASS 2
6-2193059-4	OM3	3.0	1.0	N/A	N/A	1500	500	2000	300	BLACK	TIA-492AAAC CS 115-32023 CLASS 2
6-2193059-5	OM4	3.0	1.0	N/A	N/A	3500	500	4700	550	BLACK	TIA-492AAAD CS 115-32023 CLASS 2
6-2193059-3	SINGLE-MODE BIF	N/A	N/A	0.5	0.5	N/A	N/A	N/A	N/A	BLACK	ITU-T G.657.A1

1. CABLE CONSTRUCTION:
- OPTICAL FIBER:
ALL FIBER TYPES OTHER THAN OM1 ARE BEND INSENSITIVE. SEE TABLE FOR TYPE.
 - TIGHT BUFFER: 900±50µm
COLOR CODED PER TIA-598.
 - PVC OUTER JACKET:
SEE TABLE FOR COLOR. COLOR SPECIFICATION PER EIA-359.

2. LEGEND:
- LEGEND REPEATED EVERY TWO FEET IN CONTRASTING COLOR INK.
 - SEE TABLE FOR APPROPRIATE LEGEND PRINTING.
 - MM/YY = MONTH/YEAR
 - SO XXXXXX = SHOP ORDER NUMBER.
 - XXXXX = SEQUENTIAL FOOT MARKING.

3. RATINGS:
- 3.1 UL OR ETL LISTED TYPE OFNR AND CSA FT4.
 - 3.2 QUALIFIED TO ICEA S-104-696-2001.
 - JACKET COLORS OTHER THAN BLACK ARE NOT RATED FOR DIRECT EXPOSURE TO SUNLIGHT.



LEGEND

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. BROUGHTON 05JUN13	COMMSCOPE, INC.	
DIMENSIONS: mm		CHK A. BROUGHTON 05JUN13		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. CRAIG 05JUN13	NAME CABLE, I/O DISTRIBUTION, OFNR, 2 FIBER	
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± -		WEIGHT	-	
3 PLC ± -		SIZE	A2	
4 PLC ± -		DRAWING NO	C=2193059	
ANGLES ± -		RESTRICTED TO	-	
FINISH		SCALE	NTS	
MATERIAL		SHEET	1 of 1	
-		REV	D	

2193059