

# 2055356-1 | OC-ADP-E9-E9-NNCS-AC-100

Fiber Optic Simplex Adapter, Singlemode LSH/APC, green, flanged (100 pack)

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

## Alternative products available:

760249514 Fiber Optic Simplex Adapter, Singlemode LSH/APC, green, flanged

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Product Type</b>          | Fiber adapter   |
| <b>Product Series</b>        | OC-ADP  |

## General Specifications

|                               |                              |
|-------------------------------|------------------------------|
| <b>Body Style</b>             | Simplex                      |
| <b>Color</b>                  | Green                        |
| <b>Interface</b>              | LSH/APC                      |
| <b>Mounting</b>               | Square flange                |
| <b>Total Ports, quantity</b>  | 1                            |
| <b>Transmission Standards</b> | IEC 60754-1   IEC 61300-3-42 |

## Material Specifications

|                                  |         |
|----------------------------------|---------|
| <b>Alignment Sleeve Material</b> | Ceramic |
|----------------------------------|---------|

## Mechanical Specifications

|                                 |                   |
|---------------------------------|-------------------|
| <b>Coupling Retention Force</b> | 70 N   15.737 lbf |
|---------------------------------|-------------------|

## Optical Specifications

|                                |            |
|--------------------------------|------------|
| <b>Fiber Mode</b>              | Singlemode |
| <b>Insertion Loss, maximum</b> | 0.1 dB     |

## Environmental Specifications

# 2055356-1 | OC-ADP-E9-E9-NNCS-AC-100

---

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

## Packaging and Weights

**Packaging quantity** 100

**Packaging Type** Bag

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

