760246205 | OCAB-P-S4-D315-KIT01-72F



OCAB Outdoor fiber distribution cabinet

- OCAB cabinets offers dust-proof, environmental and mechanical protection for the fiber management functions of splicing, patching and passive component integration
- Anti-vandalism features such as IK10 stainless steel material rating, reinforced door hinges preventing door removal and anti-graffiti paint finish (optional)
- Easy installable and wingnut-secured in-let plates can be custom-configured, selecting the amount of incoming, outgoing ports and PG gland sizes
- Removable top roof for possible future upgrades
- Possibility for infield repair, removable cabinet body
- Various accessories such as plinths and in-ground roots

Drop cabinet for up to 72f customer connections

- · 48 up to 72 Point-to-multipoint positions, SC & LC footprint
- · 8 branch-off blown fibre Ø5,7& 8mm microtube positions
- · 4 branch-off blown fibre Ø 12mm microtube positions
- \cdot 72 direct drops blown fibre Ø5,7 & 8mm microtube positions
- · Up to 10 OCM1 LGX Style Fiber Optic Splitter Module positions
- \cdot Transient-free, modular, flexible fibre management \cdot
- · FIST single-circuit and single-element splice trays
- · Up to 480 splices (including SC trays 160 splices)
- · Storage area for looped cable
- · Compatible with all fibre types: G.652D and G.657 series

Product Classification

Regional Availability EMEA

Product Type Fiber cross-connect hub

Product Series OCAB

General Specifications

Access Front | Single door

Color Light Gray (RAL 7035)

Mounting In-ground root | Pre-fabricated base

Dimensions

 Height
 981.4 mm | 38.638 in

 Width
 535 mm | 21.063 in

 Depth
 314.5 mm | 12.382 in

Enclosure Size Small



760246205 | OCAB-P-S4-D315-KIT01-72F

Material Specifications

Finish Powder coated polyester

Material Type Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Environmental Specifications

Environmental Space Above ground

Qualification Standards IEC 60529, IP54 | IK10

Packaging and Weights

Packaging quantity 8

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

