

G2 MPOptimate® Singlemode MPO-12 Distribution Module, 12LC APC to 1x12f MPO pinned , internal shutters

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	G2

General Specifications

Functionality	Breakout
Color, front	Green
Color, rear	Black
Interface, front	LC/APC
Interface, rear	MPO
Interface Feature, rear	Key up/down Pinned
Polarity	Method A Pairs, flipped
Shuttered	Yes
Total Fibers, quantity	12

Dimensions

Height	26.42 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	117.35 mm 4.62 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.92 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
--------------------------------	---------------------------

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.01 kg | 0.022 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

