



Fiber Optic LGX/1000 Style Singlemode Distribution Module, 20LC/APC to 1x20f MPO, Method A

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module

General Specifications

Functionality	Breakout
Adapter Color	Green
Interface, front	LC/APC + MPO
Polarity	Method A
Total Fibers, quantity	20
Total Ports, quantity, front	21
Total Ports, quantity, rear	0

Dimensions

Height	129.03 mm 5.08 in
Width	28.96 mm 1.14 in
Depth	76.2 mm 3 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	1.15 dB

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

