

C400P-BMBM

CNT-400-P CNT® Plenum Jumper with interface types BNC Male and BNC Male, variable length



Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-400

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	BNC Male
Interface, Connector B	BNC Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Nominal Size	0.400 in
---------------------	----------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–2000 MHz	1.222	20.01
2000–3000 MHz	1.288	18

Jumper Assembly Sample Label

C400P-BMBM



Included Products

- 400PBM-CR – BNC Male for CNT-400 braided cable
- CNT-400-P – CNT-400, CNT® 50 Ohm Plenum Rated Braided Coaxial Cable, white PVC jacket