

# VIP5305 | VIP5305 Compact UHD IP Set-Top

## Base Product



### IPTV, HEVC, UHD Compact Set-Top with optional 802.11ac Wi-Fi

- 4Kp60 10-bit Ultra HD with HDR support
- IPTV, OTT with HEVC decode
- Support for DVR/PVR and Time Shift through ARRIS DVR One stackable USB-connected device
- Optional 802.11ac 2x2 dual band Wi-Fi for high quality wireless video delivery
- Optional Bluetooth® Low Energy Remote Control
- Fast Boot
- Available in multiple bottom cover colors

The VIP5305 delivers a stunning Ultra High Definition video viewing experience for IPTV and OTT in a compact and stylish casing design. This set-top supports 4K UHD, High Dynamic Range (HDR), 10-bit-color with HEVC decoding. DVR and time-shift is supported through external USB devices or network DVR.

The VIP5305W variant offers additional 802.11ac Wi-Fi connectivity for high quality wireless video delivery. Optional Bluetooth® Low Energy remote control. Available in multiple bottom cover colors.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	IP video device

## General Specifications

<b>Graphics</b>	OpenGL ES2.0
<b>Hard Disk</b>	Supports DVR-One stackable disk unit
<b>Memory</b>	2 GB DRAM   512 MB Flash
<b>Network Interface</b>	Ethernet   Wi-Fi
<b>Processor</b>	14700 DMIPS
<b>Remote Interfaces</b>	Bluetooth Low Energy (optional)   IR
<b>Software Compatibility</b>	ARRIS KreaTV
<b>Tuner</b>	IP
<b>Video Formats</b>	UHD
<b>Video Decode/Encode</b>	HEVC 2160p60 10-bit   MPEG-2   MPEG-4 AVC H.264 up to MP@L4.2   VP9
<b>Video Resolution</b>	4Kp60
<b>Wi-Fi Interface Standard</b>	2x2 IEEE 802.11ac (optional)

## Dimensions

<b>Height</b>	25.908 mm   1.02 in
---------------	---------------------

# VIP5305 | VIP5305 Compact UHD IP Set-Top

---

**Diameter** 130.048 mm | 5.12 in

Logo Image



## Environmental Specifications

- Operating Temperature** 0 °C to +40 °C (+32 °F to +104 °F)
- Relative Humidity** 8%–95%
- Standards Compliance** CE | IVA | PCoC | RoHS Compliant | WEEE

## Packaging and Weights

**Weight, net** 0.209 kg | 0.46 lb