

M-Series Ruggedized Receptacle, RJ45

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Adapter kit

General Specifications

ANSI/TIA Category	5e 6 6A
Application	Provides sealed copper connectivity
Color	Black
Total Ports, quantity	1

Dimensions

Height	35.56 mm 1.4 in
Width	35.56 mm 1.4 in
Depth	25.4 mm 1 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-25 °C to +85 °C (-13 °F to +185 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
Weight, net	0.023 kg 0.05 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760042960 | MIR-RJ45

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

