



2 Port Industrial Box

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Surface mount box |

General Specifications

| | |
|------------------------------|-------------------------------------|
| ANSI/TIA Category | 5e 6 6A |
| Application | Provides sealed copper connectivity |
| Color | Gray |
| Mounting | Surface |
| Total Ports, quantity | 1 |

Dimensions

| | |
|---------------------------|--------------------|
| Height | 119.38 mm 4.7 in |
| Width | 78.74 mm 3.1 in |
| Depth | 82.55 mm 3.25 in |
| Plug Diameter | 29.21 mm 1.15 in |
| Receptacle Opening | 27.94 mm 1.1 in |

Material Specifications

| | |
|----------------------|----------|
| Material Type | Aluminum |
|----------------------|----------|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -25 °C to +85 °C (-13 °F to +185 °F) |
| Flammability Rating | UL 94 V-0 |

760080820 | MIB-2

Qualification Standards IEC 60529, IP65

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Weight, net 0.544 kg | 1.2 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

