


MGS Icon Strip (Voice / Data / Blank), Black (25 ea/pkg)



## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Icon kit

## General Specifications

<b>Color</b>	Black
--------------	-------

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	500
---------------------------	-----

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

UK-ROHS

Compliant

