

MGS Icon Strip (Voice / Data / Blank), Yellow (25 ea/pkg)



Product Classification

Regional Availability	North America
Portfolio	SYSTIMAX®
Product Type	Icon kit

General Specifications

Color	Yellow
--------------	--------

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	500
---------------------------	-----

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

760103796 | M61K-ICON-YL

UK-ROHS

Compliant

