# 760104737 | 360-RCM-RM

Man and water

SYSTIMAX 360™ Rear Cable Management, rack mountable

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America	
Portfolio	SYSTIMAX®	
Product Type	Cable management hardware	
Product Brand	GigaSPEED X10D®	

#### General Specifications

Color

Clear | Silver

### Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

# **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL   cUL

## Packaging and Weights

Packaging quantity

#### 1

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025



# 760104737 | 360-RCM-RM



Compliant



©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025

**COMMSCOPE**°