

# 360000017 | 8.5mm/6mm PLENUM DUCT EMPTY

---

E20® Empty Conduit, 8.5 mm, opaque white



## Product Classification

<b>Product Type</b>	Empty conduit
<b>Product Brand</b>	E20®
<b>Warranty</b>	One year

## General Specifications

<b>Color</b>	Opaque white
<b>Conduit Type</b>	Non-toneable
<b>Density, maximum</b>	0.955 g/cm <sup>3</sup>   0.035 lb/in <sup>3</sup>
<b>Density, minimum</b>	0.941 g/cm <sup>3</sup>   0.034 lb/in <sup>3</sup>
<b>Design Standard</b>	ASTM D3350-05
<b>Wall Type</b>	Smooth

## Dimensions

<b>Length</b>	762 m   2500 ft
<b>Inner Diameter, nominal</b>	6.096 mm   0.24 in
<b>Outer Diameter, nominal</b>	8.509 mm   0.335 in
<b>Wall Thickness, minimum</b>	1.143 mm   0.045 in
<b>Nominal Size</b>	8.5 mm

## Material Specifications

<b>Material Type</b>	PVDF
----------------------	------

## Mechanical Specifications

<b>Minimum Bend Radius, unsupported</b>	330.2 mm   13 in
<b>Tensile Strength at yield, minimum</b>	20.684 N/mm <sup>2</sup>   3000 psi

# 360000017 | 8.5mm/6mm PLENUM DUCT EMPTY

---

**Pulling Tension, maximum** 80.286 kg | 177 lb

## Packaging and Weights

**Weight, net** 0 kg/km | 0 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines