

7801330 | SFP+, 10GBase CWDM-470, up to 40 km



Small form factor pluggable+ Module, 10G BASE, CWDM, Singlemode

Product Classification

Product Type	Optical module
Product Series	SFP+

General Specifications

Interface	LC/UPC
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

Dimensions

Height	12 mm 0.472 in
Width	14 mm 0.551 in
Depth	57 mm 2.244 in

Optical Specifications

Fiber Type	9/125 μ m, singlemode
Average Optical Output Power, maximum	4 dBm
Average Optical Output Power, minimum	-1 dBm
Rx/Tx Power Accuracy	\pm 3dB / \pm 3dB
Operating Wavelength	1260 – 1620 nm (Rx) 1471 nm
Receiver Sensitivity at Bandwidth Range	-15.8 dBm @ 9.95–10.5 Gb/s
Receiver Overload	-1 dBm

Environmental Specifications

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
------------------------------	------------------------------------

Packaging and Weights

Height, packed	20 mm 0.787 in
-----------------------	------------------

7801330 | SFP+, 10GBase CWDM-470, up to 40 km

Width, packed	105 mm 4.134 in
Depth, packed	65 mm 2.559 in
Packaging quantity	1
Packaging Type	Box
Weight, gross	0.036 kg 0.079 lb
Weight, net	0.022 kg 0.049 lb