


# EG8892-000 | OCC1P-10800-NNNQQA-A2



OCC1P Wideband Splitter, planar, singlemode, 1x8, symmetrical split ratio, 0,250 mm cable, light duty housing

## OBSOLETE

This product was discontinued on: July 25, 2023

### Replaced By:

F08852-000	OCC1P Wideband Splitter, planar, singlemode, 1x8, symmetrical split ratio, 0,250 mm cable, light duty housing
OCC1P-10800-NNNQQA	

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Splitter component
<b>Product Series</b>	OCC1P

## General Specifications

<b>Device Type</b>	Component, rectangular
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 8 splitter
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Pigtail Length, Input</b>	2.5 m   8.202 ft
<b>Pigtail Length, Output</b>	2.5 m   8.202 ft
<b>Pigtail Diameter, Input</b>	0.25 mm   0.01 in
<b>Pigtail Diameter, Output</b>	0.25 mm   0.01 in

## Environmental Specifications

**Qualification Standards**      Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

## Packaging and Weights

**Packaging quantity**                      1