



## L Type Flush Mounted Faceplate, four port black

- Available for use with the DYMO® labeling solution

### Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Faceplate kit   |
| <b>Product Series</b>        | M Series  |

### General Specifications

|                              |   |
|------------------------------|---|
| <b>Application</b>           | Used with M Series modular information outlet |
| <b>Color</b>                 | Black   |
| <b>Mounting</b>              | Flush   |
| <b>Total Ports, quantity</b> | 4   |

### Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 115.824 mm   4.56 in |
| <b>Width</b>  | 71.374 mm   2.81 in  |
| <b>Depth</b>  | 7.366 mm   0.29 in   |

### Material Specifications

|                      |   |
|----------------------|---|
| <b>Material Type</b> | High-impact, flame retardant, thermoplastic |
|----------------------|---|

### Environmental Specifications

|                            |           |
|----------------------------|-----------|
| <b>Flammability Rating</b> | UL 94 V-0 |
| <b>Safety Standard</b>     | UL   cUL  |

### Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 0.036 kg | 0.08 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

