2153216-3



MiniPod, category 6, 3 port, unloaded with angled adapters, unshielded

- Improved speed of redeployment in the workplace through rapid mechanism
- Simplified cabling of raised floor spaces and ideal for high density environments
- Ideal to be terminated at an early stage in the building works
- Designed for use with all standard flexible conduit systems

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio NETCONNECT®

Product Type Modular jack enclosure

Product Series MiniPod

General Specifications

ANSI/TIA Category 6

Application Used with KJ Series outlets

Cable Entry LocationSideColorBlack

Conduit Fitting Size 25.1 mm | 0.988 in

Integrated Dust Cover TypeSlidingMountingSurfaceOutlet OrientationFlatTotal Ports, quantity3

Dimensions

 Height
 47 mm | 1.85 in

 Width
 185 mm | 7.283 in

 Depth
 50 mm | 1.969 in

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS)

COMMSCOPE®

2153216-3

Environmental Specifications

Environmental Space Indoor
Flammability Rating UL 94 V-0

Packaging and Weights

Included Angled Keystone Adaptor (3) | Clear Label Window (3) | Label Insert (3) | MiniPod

Subassembly (1) | Mounting screw (1)

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

