

TeraSPEED® LC UniBoot 2.0MM UPC/LC UNIBOOT CONNECTOR KIT

OBSOLETE

This product was discontinued on: June 29, 2022

Replaced By:

860658160

LC/UPC Uniboot Connector, Singlemode, Blue

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	SYSTIMAX ULL TeraSPEED®
Product Series	Uniboot

General Specifications

Body Style	Duplex
Color	Blue
Interface	LC/UPC
Interface Feature	Uniboot

Dimensions

Compatible Cable Diameter	2 mm 0.079 in
---------------------------	-----------------

Material Specifications

Ferrule Material	Zirconia
------------------	----------

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
-----------------------------------	---------------------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D G.657.A2 OS2
Insertion Loss Change, mating	0.25 dB

Optical Components Standard	ANSI/TIA-568-C.3
Insertion Loss, ULL, maximum	0.25 dB
Return Loss, minimum	50 dB

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings