

CZ8125-000 | RFP-1-60-S2-1-L-C-TE



RapidFiber® Faceplate, SC/APC, 60 meters cable on spool, cavity mount

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Faceplate kit
Product Brand	RapidFiber®
Product Series	RFP

General Specifications

Color	White
Cover Type	Hinged with latches
Interface Type	SC/APC
Mounting	Cavity mount
Port Capacity, maximum	2
Total Ports, quantity	1

Dimensions

Height	74.93 mm 2.95 in
Width	115.062 mm 4.53 in
Depth	14.986 mm 0.59 in
Cable Length	60 m 196.85 ft
Cable Diameter	1 mm 0.039 in

Material Specifications

Material Type	LSZH thermoplastic
----------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

CZ8125-000 | RFP-1-60-S2-1-L-C-TE

Fiber Type G.657.B3

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

