



Fiber Optic Easy Faceplate, SC/UPC

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Latin America   North America
<b>Product Type</b>	Fiber wall outlet
<b>Product Series</b>	SFP

## General Specifications

<b>Color</b>	White
<b>Cover Type</b>	Snap-on cover
<b>Interface Type</b>	SC/UPC
<b>Mounting</b>	Wall mount
<b>Total Ports, quantity</b>	1

## Dimensions

<b>Height</b>	98.044 mm   3.86 in
<b>Width</b>	50.038 mm   1.97 in
<b>Depth</b>	20.066 mm   0.79 in

## Material Specifications

<b>Material Type</b>	LSZH thermoplastic
----------------------	--------------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

**Environmental Space** Indoor

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

