FGS-ACC137





FiberGuide® Vertical Straight Section with 1.5in Slot Spacing, Cover, End Cap and Mounting Brackets, 2x2in, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Slotted vertical with snap-on cover

Product Brand FiberGuide®

Product Series FGS

General Specifications

Product Feature Snap-together design

Color Yellow
Orientation Vertical

Section Type Straight section

Dimensions

 Height
 50.8 mm | 2 in

 Width
 50.8 mm | 2 in

Length 1829 mm | 72.008 in

System Dimensions 51 mm x 51 mm (2 in x 2 in)

Material Specifications

Material Type Steel

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Regulatory Compliance/Certifications

COMMSCOPE®

FGS-ACC137

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

