FGS-KTW2-D-IMP-B



FiberGuide® Vertical Duct Kit with 4in Slot Spacing, Spools and Split See-Through Cover, 4x4in, Yellow

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Slotted vertical with snap-on cover

Product Brand FiberGuide®

Product Series FGS

General Specifications

Product Feature Slotted

Color Yellow

Orientation Vertical

Section Type Straight Section

Dimensions

 Height
 115 mm | 4.528 in

 Width
 120 mm | 4.724 in

 Length
 1829 mm | 72.008 in

System Dimensions 102 mm x 102 mm (4 in x 4 in)

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

COMMSCOPE®

FGS-KTW2-D-IMP-B

Weight, net 6.643 kg | 14.645 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

