

FGS-MSHS-F100MM



FiberGuide® Horizontal Straight Section, 4x12in, 100mm Length, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Straight section
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Yellow
Orientation	Horizontal
Section Type	Straight section

Dimensions

Height	102 mm 4.016 in
Width	347 mm 13.661 in
Length	100 mm 3.937 in
System Dimensions	102 mm x 305 mm (4 in x 12 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net	0.324 kg 0.714 lb
--------------------	---------------------

FGS-MSHS-F100MM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

