

FGSB-MFTY-25F



FiberGuide® 7/8in Flex Tube, Slotted, 25ft Length, Black

OBSOLETE

This product was discontinued on: October 1, 2023

Replaced By:

FGSB-MFTY-50F FiberGuide® 7/8in Flex Tube, Slotted, 50ft Length, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Convoluted tube
Product Brand	FiberGuide®
Product Series	FGS

General Specifications


Product Feature	Round
Color	Black
Orientation	Vertical
Section Type	Vertical section

Dimensions

Length	7620 mm 300 in
Tube Outer Diameter	567.69 mm 22.35 in

Ordering Tree

FGSB-MFTY-25F



Tube Color

9	empty	yellow
	B	black

Tube Length, examples

11	5F	5 feet
	350F	350 feet

Tube Type

10	MIDY	Slotted flexible tube, 2 in diameter
	MFTY	Slotted flexible tube, 7/8 in diameter
	MISY	Solid flexible tube, 2 in diameter
	MLDY	Slotted flexible tube, 1 in diameter

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net	0.256 kg 0.564 lb
--------------------	---------------------

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

