

FGSB-MIDY-200F



FiberGuide® 2in Flex Tube, Slotted, 200ft Length, Black

OBSOLETE

This product was discontinued on: October 1, 2023

Replaced By:

FGSB-MIDY-250F FiberGuide® 2in Flex Tube, Slotted, 250ft Length, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Convolute tube
Product Brand	FiberGuide®
Product Series	FGS

General Specifications


Color	Black
Orientation	Vertical
Section Type	Vertical section

Dimensions

Length	60960 mm 2,400.001 in
Tube Outer Diameter	50.8 mm 2 in

Ordering Tree

FGSB-MIDY-200F



Tube Color

9	empty	yellow
	B	black

Tube Length, examples

11	5F	5 feet
	350F	350 feet

Tube Type

10	MIDY	Slotted flexible tube, 2 in diameter
	MFTY	Slotted flexible tube, 7/8 in diameter
	MISY	Solid flexible tube, 2 in diameter
	MLDY	Slotted flexible tube, 1 in diameter

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net 11.267 kg | 24.839 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

