



CWST wraparound repair sleeve heat shrink kit, unpresurized, for 42 to 164 mm cable diameter, 1000 mm long

- Excellent split resistance of the composite structure offers superior resistance to mechanical abuse during and after the installation
- Integrated moisture barrier completely reconstitutes the cable sheath construction

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink repair sleeve
Product Series	CWST

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Length	1000 mm 39.37 in
Expanded Inside Diameter, minimum	164 mm 6.457 in
Recovered Inside Diameter, maximum	42 mm 1.654 in
Single Cable Diameter, maximum	164 mm 6.457 in
Single Cable Diameter, minimum	42 mm 1.654 in
Expanded Wall Thickness, minimum	1.1 mm 0.043 in

Material Specifications

Material Type	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

Environmental Specifications

Environmental Space Aerial | Buried | Ducted

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Weight, net 1.1 kg | 2.425 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

