



4 in boot cushion insert with 1 hole for HELIAX® cables (Fusion tape included)

## Product Classification

<b>Product Type</b>	Cushion insert
<b>Product Brand</b>	I-Line
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Cable Type</b>	Hybrid fiber
<b>Cables per Cushion</b>	1
<b>Color</b>	Black

## Dimensions

<b>Height</b>	82.55 mm   3.25 in
<b>Length</b>	25.4 mm   1 in
<b>Nominal Size</b>	1-1/4 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Environmental Specifications

<b>UV Resistance Test Method</b>	MIL-STD-810E, Procedure 11, Method 505
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66

## Packaging and Weights

<b>Height, packed</b>	170.18 mm   6.7 in
<b>Width, packed</b>	129.54 mm   5.1 in
<b>Length, packed</b>	99.06 mm   3.9 in
<b>Included</b>	Cushion

# 294701-T

---

**Packaging quantity** 1  
**Weight, gross** 0.5 kg | 1.102 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

## Included Products

FT-TB – Black Self-fusing Tape, 15 ft