

760235790 | FOSC-OC-6DBD1411NN2T-U23

FOSC® A-TRAY-24 type, DWDM, 8 channels + upgrade port, demux, 1544.53 nm starting wavelength, 100 GHz channel spacing



Product Classification

Regional Availability	North America
Product Type	DWDM splice tray
Product Brand	FOSC®
Product Series	FOSC-OC

General Specifications

Application	For use in FOSC closures
Interface, Input	Stub tail
Interface, Output	Stub tail

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

