

209800-28B



Self-locking Hanger for 7/8 in RXL5 RADIAX® Radiating cable

Product Classification

Product Type Hanger kit

General Specifications

Cables per Hanger 1
Color Black
Hanger Type Self locking hanger

Dimensions

Maximum Stack Height 2
Height 49 mm | 1.929 in
Width 20.3 mm | 0.799 in
Length 33.5 mm | 1.319 in
Compatible Diameter, maximum 31.2 mm | 1.228 in
Compatible Diameter, minimum 27.8 mm | 1.094 in
Nominal Size 7/8 in

Material Specifications

Material Type Polyamide PA12

Mechanical Specifications

Maximum Load 850 N | 191.088 lbf

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)
Flammability Test Method UL 94-HB
Toxicity Index Test Method IEC 60754-2
UV Resistance, minimum with no degradation ≥500 hours exposure in accelerated UV life chamber

209800-28B

Packaging and Weights

Height, packed	19 cm 7.48 in
Width, packed	11 cm 4.331 in
Length, packed	16.5 cm 6.496 in
Packaging quantity	50
Weight, gross	0.88 kg 1.94 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power