

# 209800-36B

---



Self-locking Hanger for 1-1/4 in RADIAX® Radiating cable

## Product Classification

**Product Type** Hanger kit

## General Specifications

**Cables per Hanger** 1  
**Color** Black  
**Hanger Type** Self locking hanger

## Dimensions

**Maximum Stack Height** 2  
**Height** 59.4 mm | 2.339 in  
**Width** 21.1 mm | 0.831 in  
**Length** 41.9 mm | 1.65 in  
**Compatible Diameter, maximum** 39.5 mm | 1.555 in  
**Compatible Diameter, minimum** 35.5 mm | 1.398 in  
**Nominal Size** 1-1/4 in

## Material Specifications

**Material Type** Polyamide PA12

## Mechanical Specifications

**Maximum Load** 1200 N | 269.771 lbf

## Environmental Specifications

**Operating Temperature** -40 °C to +80 °C (-40 °F to +176 °F)  
**Flammability Test Method** UL 94-HB  
**Toxicity Index Test Method** IEC 60754-2  
**UV Resistance, minimum with no degradation** ≥500 hours exposure in accelerated UV life chamber

# 209800-36B

---

## Packaging and Weights

<b>Height, packed</b>	11.5 cm   4.528 in
<b>Width, packed</b>	14.5 cm   5.709 in
<b>Length, packed</b>	25 cm   9.843 in
<b>Packaging quantity</b>	50
<b>Weight, gross</b>	1.12 kg   2.469 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power