

243095-12

Stainless Steel Hardware Kit for 1-1/4 in or 1-5/8 in Double Click-on Hangers, includes M10 bolts and hardware, 125.98 mm (4.96 in) length



Product Classification

Product Type	Hardware kit
Ordering Note	CommScope® non-standard product

General Specifications

Thread Size	M10
--------------------	-----

Dimensions

Maximum Stack Height	1
Length	125.984 mm 4.96 in
Nominal Size	1-1/4 in 1-5/8 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Packaging and Weights

Height, packed	129.54 mm 5.1 in
Width, packed	30.48 mm 1.2 in
Length, packed	30.48 mm 1.2 in
Included	Forty flat washers Forty lock washers Ten M10 threaded rods Twenty hex nuts
Packaging quantity	10
Weight, gross	1.302 kg 2.87 lb

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power