

68MCLICK



Miniature Click-on Hanger for 6–8 mm cable

Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Click-on hanger
Mounting	M8 through hole

Dimensions

Maximum Stack Height	3
Height	38.1 mm 1.5 in
Width	16 mm 0.63 in
Length	35.1 mm 1.382 in
Compatible Cable Diameter Range	5.8–8.1 mm
Compatible Diameter, maximum	8.1 mm 0.319 in
Compatible Diameter, minimum	5.8 mm 0.228 in
Nominal Size	1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

68MCLICK

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 30.4 cm | 11.969 in

Width, packed 27.9 cm | 10.984 in

Length, packed 2.5 cm | 0.984 in

Packaging quantity 10

Weight, gross 0.09 kg | 0.198 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power