

CY1080-000 | FIST-FCASA2-FC471NN-L



FIST® Fiber Splice Tray with Field Installable CWDM, 8 Channels and 1310nm port, compact CWDM, 1471nm starting wavelength, 20nm channel spacing, all fibers at left side

Product Classification

Regional Availability	EMEA
Product Type	CWDM splice tray
Product Brand	FIST®
Product Series	FIST-FCASA2

General Specifications

Application	For use with FIST fiber splice closures For use with FIST panels
Interface, Input	Stub tail
Interface, Output	Stub tail

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

