

# FA-2628-SIH

---



## Snap-In Hanger and Grommet kit for HELIAX® Cables, 26-28mm

### Product Classification

|                      |                                 |
|----------------------|---------------------------------|
| <b>Product Type</b>  | Hanger kit                      |
| <b>Ordering Note</b> | CommScope® non-standard product |

### General Specifications

|                          |                                   |
|--------------------------|-----------------------------------|
| <b>Cables per Hanger</b> | 1                                 |
| <b>Color</b>             | Black   Silver                    |
| <b>Hanger Type</b>       | Hanger kits                       |
| <b>Mounting</b>          | 3/8 in (M10) drilled cable ladder |

### Dimensions

|                                        |                    |
|----------------------------------------|--------------------|
| <b>Maximum Stack Height</b>            | 3                  |
| <b>Height</b>                          | 58.9 mm   2.319 in |
| <b>Width</b>                           | 38.1 mm   1.5 in   |
| <b>Length</b>                          | 76.2 mm   3 in     |
| <b>Compatible Cable Diameter Range</b> | 26–28 mm           |
| <b>Compatible Diameter, maximum</b>    | 28 mm   1.102 in   |
| <b>Compatible Diameter, minimum</b>    | 26 mm   1.024 in   |
| <b>Nominal Size</b>                    | 1-1/4 in           |

### Electrical Specifications

|                                    |        |
|------------------------------------|--------|
| <b>Return Loss Effect, maximum</b> | 0.1 dB |
| <b>DTF Effect, maximum</b>         | 0.1 dB |

### Material Specifications

|                      |                               |
|----------------------|-------------------------------|
| <b>Material Type</b> | EPDM rubber   Stainless steel |
|----------------------|-------------------------------|

### Mechanical Specifications

# FA-2628-SIH

---

## Vibration Survival

≥4 hours at resonant frequency

## Environmental Specifications

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

### Environmental Strength Capability

Double cable weight

## Packaging and Weights

### Height, packed

26 cm | 10.236 in

### Width, packed

9 cm | 3.543 in

### Length, packed

9 cm | 3.543 in

### Packaging quantity

10

### Weight, gross

0.53 kg | 1.168 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power