

L1SGRIP



Support Hoisting Grip with clamp for 0.32-0.44 in (8.2-11.2 mm) coaxial cable

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Installation Tool	Required, not included
Support Clamp	Included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	101.6 mm 4 in
Leader Length, minimum	152.4 mm 6 in
Compatible Diameter, maximum	11.2 mm 0.441 in
Compatible Diameter, minimum	8.2 mm 0.323 in
Nominal Size	1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel Tin-coated bronze
----------------------	-------------------------------------

Mechanical Specifications

Pull Load Capacity	158.757 kg 350 lb
---------------------------	---------------------

L1SGRIP

Packaging and Weights

Height, packed	25.4 mm 1 in
Width, packed	177.8 mm 7 in
Length, packed	127 mm 5 in
Packaging quantity	1
Weight, gross	0.3 kg 0.661 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

