

SCPTW16



Small Cell Antenna Pole Top Mount with 16" Standoff (for Poles 8in to 10in OD)

Product Classification

Product Type Pole mount kit | Wood pole mount

General Specifications

Mounting Wood pole

Dimensions

Height 513.08 mm | 20.2 in

Width 254 mm | 10 in

Length 254 mm | 10 in

Mounting Diameter, maximum 254 mm | 10 in

Mounting Diameter, minimum 203.2 mm | 8 in

Stand-off Distance 406.4 mm | 16 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Attachment hardware | Universal Small Cell Antenna Bracket – see drawing for compatible models

Packaging quantity 1

Regulatory Compliance/Certifications

SCPTW16

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS



Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code