DLX-OPT-CONV-25

DLX to hardened full-size Converter



• Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Fiber converter

Product Brand DLX®
Product Series FHD

General Specifications

Interface, Connector A Hardened mini-size DLX

Interface, Connector B Hardened full-size SC/APC

Optical Specifications

Insertion Loss, maximum0.5 dBReturn Loss, minimum65 dB

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Qualification Standards Telcordia GR-326-CORE

Packaging and Weights

Packaging quantity 25

Regulatory Compliance/Certifications

Agency	Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



DLX-OPT-CONV-25



