



FIST Gel Sealing Kit for round splice closure port, sealing 3 cables with diameter between 6.5 and 8 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

Product Classification

Regional Availability	EMEA
Product Type	Gel sealing kit
Product Series	FIST-GC02
Ordering Note	Cable jackets containing flame retardant components are advised to be combined with the Silicone gel multi-out seal

General Specifications

Application	For use with FIST-GC02 Fiber closures
Cable Capacity, maximum	3
Color	Black

Dimensions

Single Cable Diameter, maximum	8 mm 0.315 in
Single Cable Diameter, minimum	6.5 mm 0.256 in

Packaging and Weights

Included	Cable termination brackets Dummy plugs Multi-out gel seal
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

UK-ROHS

Compliant/Exempted

