CB-12-16LH



Cable banding, 1/2 in x 16 in length with attached locking head, package contains 50 pieces

Product Classification

Product Type Banding

Ordering Note CommScope® standard product (Global)

General Specifications

Adapter Type Adapter
Color Black

Mounting Round member

Dimensions

 Width
 12.7 mm | 0.5 in

 Length
 0.405 m | 1.33 ft

 Material Thickness
 1.524 mm | 0.06 in

Material Specifications

Material Type Heat-stabilized weather resistant acetal

Mechanical Specifications

Tensile Force 1,112.055 N | 250 lbf

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

Packaging quantity 50

