

FGSB-FLEXV-4F-A2C



FiberGuide® FlexVertical Dual Kit, 4x4 to Dual 2x2in, 4ft Length, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Drop kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Snap-together design
Angle/Bend Direction	30°
Color	Black
Orientation	Vertical
Section Type	Vertical section

Dimensions

Height	1,447.038 mm 56.97 in
Width	107.95 mm 4.25 in
Length	172.618 mm 6.796 in
System Dimensions	102 mm x 102 mm (4 in x 4 in) 51 mm x 51 mm (2 in x 2 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

FGSB-FLEXV-4F-A2C

Packaging and Weights

Included	Hardware
Packaging quantity	1
Weight, net	2.812 kg 6.199 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

