

FGS-KT07-A4-10F



FiberGuide® Quad 7/8in Flex Tube Attachment, 4x4in, 10ft Length, Yellow

OBSOLETE

This product was discontinued on: October 1, 2023

Replaced By:

FGS-KT07-A4-15F	FiberGuide® Quad 7/8in Flex Tube Attachment, 4x4in, 15ft Length, Yellow
FGS-MIDY-200F	FiberGuide® 2" Flex Tube, Slotted, 200ft Length, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Convolute tube
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Round
Color	Yellow
Orientation	Vertical
Section Type	Adapter

Dimensions

Height	101.6 mm 4 in
Width	101.6 mm 4 in
Length	3048 mm 120 in
Tube Outer Diameter	22.35 mm 0.88 in
System Dimensions	102 mm x 102 mm (4 in x 4 in)

FGS-KT07-A4-10F

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net	2.965 kg 6.537 lb
--------------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

