



Fiber Optic Termination/Splice Panel, 1U, 19 in, unloaded for 48 LC duplex or 48 SC simplex, black

Product Classification

Regional Availability	Asia Australia/New Zealand China India
Portfolio	CommScope®
Product Type	Fiber patch/splice panel

General Specifications

Functionality	Patching Splicing
Body Style	Symmetrical
Cable Exit Location	Rear
Color	Black
Color, front	Black
Growth Configuration	Unloaded
Interface, front	LC SC
Interface Feature, front	Standard
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Splice Trays Included, quantity	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	320 mm 12.598 in

Material Specifications

Finish	Powder coated
Material Type	Steel

760249182

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1