

FDC-L2JUSX20101040



FDC Fiber Optic Wall Box, 24-position, Singlemode SC/APC

Product Classification

Regional Availability	North America
Product Type	Fiber wall box
Product Series	FDC

General Specifications

Functionality	Patching Splicing
Access	Front
Application	Accepts LGX-style Value Added Modules
Cable Type	Pigtails - Stranded
Enclosure Color	Putty white
Interface	SC/UPC
Mounting	Wall
Port, quantity	24

Dimensions

Height	610 mm 24.016 in
Width	503 mm 19.803 in
Depth	177.04 mm 6.97 in

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Outdoor
Qualification Standards	NEMA, Type 4

FDC-L2JUSX20101040

Packaging and Weights

Included	Compression fitting Tie-off adapter
Packaging quantity	1
Packaging Type	Box Carton