

# FDT-BN212NXB000A



iFDT Indoor Fiber Distribution Terminal, 24-fiber, 12 adapters, SC/UPC, soft-wall pigtails, heat shrink splice trays, W/key lock

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution terminal
<b>Product Series</b>	IFDT

## General Specifications

<b>Adapters, quantity</b>	24
<b>Cable Entry Location</b>	Bottom right   Top right
<b>Cable Type</b>	Pigtails - Stranded
<b>Color</b>	Putty white
<b>Front Door Type</b>	Double hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface</b>	SC/UPC
<b>Lock Type</b>	Padlock ready
<b>Mounting</b>	Wall
<b>Port, quantity</b>	24
<b>Splice Tray Chip Type</b>	Heat shrink
<b>Splicing Capacity, maximum</b>	24

## Dimensions

<b>Height</b>	203.2 mm   8 in
<b>Width</b>	355.6 mm   14 in
<b>Depth</b>	127 mm   5 in

## Ordering Tree

# FDT-BN212NXB000A



## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Qualification Standards</b>	NEMA, Type 12   Telcordia GR-2898-CORE

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

# FDT-BN212NXB000A

---

## Regulatory Compliance/Certifications

**Agency**

UK-ROHS

**Classification**

Compliant/Exempted